

Chip extraction system

Keeping your work area clean.

- **Powerful HP drive or electric motor**
- **Impeller made of solid steel**
- **Mobile** thanks to solid rubber wheels \varnothing 30 cm and transport handle
- **High air flow performance** – up to 1,500 m³/h*
- **Dimensions** 67 × 75 × 107 cm (l × w × h)
- **2-m suction hose** \varnothing 15 cm and **10-m pressure hose** \varnothing 15 cm
- **Reducing ring** from \varnothing 15 to \varnothing 10 cm for the suction hose
- **Rotation range** of pressure joint 270° in 10 steps
- **Perfect in combination with our Zyklon 350** for firewood processors up to a log diameter of max. 41 cm (e.g. POSCH SpaltFix S-375, K-415, S-415) as well as log saws, automatic firewood saws and firewood processor

Case rotatable



TIP:

The collected chips can be processed further.

Chip extraction system 350S

The chip extraction system can be used in combination with all circular saws, automatic firewood saws (e.g. POSCH EasyCut, SmartCut, AutoCut) and firewood processors (e.g. POSCH SpaltFix – up to and incl. SpaltFix S-415).

Article no.	Type	Drive	Weight kg
M7386	E3-400	3 kW E-motor 400V, S1, CEE 16A Incl. switch with 10m cable to operate the chip extraction on the saw. ! Please note: The blower must not be used in enclosed spaces!	~ 101
M7387	PS	Tractor hydraulics, size 3 hydraulic sleeve for forward and return movement required. Incl. current regulator, hydraulic free wheeling system and geared motor, 2,800 rpm. Hydraulic connection for 20 – 60l/min., max. 150 bar. ! Please note: The blower must not be used in enclosed spaces!	~ 95

ⓘ Matching chip extraction connectors are listed next to the respective saw in the “accessories” table.

Chip extraction system accessories

Article no.	Name
F0002791	\varnothing 10 cm chip extraction connector for tilting table saw without three-point extension, model “G/H”
F0004604	\varnothing 10 cm chip extraction connector for tilting saw with conveyor belt with three-point extension
F0003773	\varnothing 10 cm chip extraction connection for tilting saw without three-point extension, model H/HS
F0002195	\varnothing 15 cm chip extraction connection 15 cm for tilting saw PLUS
F0004088	\varnothing 10 cm chip extraction connection for rolling table saw and UniCut with three-point extension
F0002860	\varnothing 10 cm chip extraction connection for roller bench saw and UniCut without three-point extension
F0004426	\varnothing 15 cm chip extraction connection for WippCut
F0004069	Reducing ring from \varnothing 15 cm to \varnothing 10 cm for the chip extraction connector, matching SpaltFix S-375

Chip extraction unit for circular saws and SpaltFix (up to and incl. SpaltFix S-415)



The accruing chips are extracted by means of a suction hose (\varnothing 15 cm) and a pressure hose (\varnothing 15 cm).



The extraction system is highly flexible thanks to its transport handle and solid rubber wheels.



In just a few steps, the pressure joint can be adjusted by a total of 270 °.